



GD 375-S

E-NR: 6332538

Este producto ha sido discontinuado y reemplazado por: [GD 475-SJ](#)

El GD 375-S tiene las mismas características que GD 375 con salida de transistor y se conecta al panel de control mediante la unidad de interfaz IU 300.
El detector tiene un cable en espiral con conector modular que se conecta a la caja de conexiones JB 103-4, lo que le permite desconectado rápida y fácilmente del circuito detector, cuando por ejemplo se tienen que limpiar las ventanas.

ADDITIONAL INFORMATION

Voltaje entrada	polaritetsberoende
Indicación alarma	LED
Temperatura de funcionamiento	-40 – +70°C
Grado de protección	IP 67
Dimensiones (L x W x H) mm	91 x 31 x 23
Dimensiones (H x Ø) mm	11 x 27

ORDER INFORMATION

Model	E-NR	Description
GD 375-S	6332538	Glass break detector for laminated glasswith transistor output, glued, coiled cablewith 4-pin modular connector plug
GD 375-SJ	6332539	Glass break detector for laminated glasswith transistor output, glued, coiled cablewith 4-pin modular connector plug and junctionbox JB 103-4



SCHEMATICS

